

TECHNICAL CUSTOMER INFORMATION

April 2019

Tempered Dosing Augers for ROVEMA Form, Fill and Seal Machines


Dear customer,

Due to the abrasiveness of the product to be packed, dosing augers are subject to constant wear. A worn auger leads to deviations in the dosing and weight accuracy and thus has to be exchanged regularly.

Thanks to innovative manufacturing methods and a new stainless steel alloy we can now offer you tempered dosing augers. This considerably prolongs the product life and thus also the change intervals of the auger. Moreover, the wear of the edges does not cause flow chip, which reduces the number of inspection intervals to a minimum.

A tempered dosing auger offers you:

- reduction of wear and the risk of product contamination through flow chip to a minimum
- considerably longer product life
- less exchanges of auger thanks to a longer durability
- reduction of downtimes and the risk of production loss
- ensured dosing and weight accuracy



dosing auger

scope of delivery:

- tempered dosing auger, same size and execution as already existing

We will gladly issue an offer also for a complete auger forming set with a tempered auger including tube and corresponding closing device like already existing in your machine.

For more information about tempered dosing augers or in case of questions regarding your ROVEMA packaging machine, your contact persons at ROVEMA Service are always at your disposal.

Your ROVEMA Service Team